



Double ended ring spanner, straight, for Torx® screws, Torx® profile: E14XE18



Order data

Order number	619400 E14XE18
GTIN	4018754022366
Item class	63A

Description

Version:

Drop forged, straight design. Flat heads and thin rings for restricted places. Fluted shaft.

Material:

Chrome alloy steel, chrome-plated over nickel.

Spanner length L: 185 mm

maximum ring $\varnothing D_1$ max: 17.8 mm

maximum ring $\varnothing D_2$ max: 22.5 mm

maximum ring height $h_{1\max}$: 8 mm

maximum ring height $h_{2\max}$: 9.5 mm

Technical description

maximum ring $\varnothing D_1$ max	17.8 mm
Torx® profile 2	E18
Spanner length L	185 mm
maximum ring height $h_{1\max}$	8 mm
maximum ring $\varnothing D_2$ max	22.5 mm
Torx® profile 1	E14
maximum ring height $h_{2\max}$	9.5 mm
Manufacturing process	drop forged
Material	Chrome alloy steel
Type of product	Spanner

