



## Double-ended open ring spanner, Width across flats: 17X19mm



### Order data

Order number	619705 17X19
GTIN	4045197673398
Item class	62A

### Description

#### Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

#### Standard:

**DIN 3118 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Spanner length L	213 mm
maximum ring height $h_{1\max}$	12 mm
maximum ring $\varnothing D_1 \max$	31.2 mm
Width across flats 2	19 mm
maximum ring height $h_{2\max}$	13 mm
maximum ring $\varnothing D_2 \max$	33.3 mm
Width across flats 1	17 mm
Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10 degrees

## Data sheet

Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner