



Double-ended open ring spanner, Width across flats: 17X19 mm



Order data

Order number	619705 17X19
GTIN	4045197673398
Item class	62A

Description

Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

Standard:

DIN 3118 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 213 mm

maximum ring $\varnothing D_1$ max: 31.2 mm

maximum ring $\varnothing D_2$ max: 33.3 mm

maximum ring height $h_{1\max}$: 12 mm

maximum ring height $h_{2\max}$: 13 mm

Technical description

Spanner length L	213 mm
maximum ring height $h_{1\max}$	12 mm
maximum ring $\varnothing D_1$ max	31.2 mm
Width across flats 2	19 mm
maximum ring height $h_{2\max}$	13 mm
maximum ring $\varnothing D_2$ max	33.3 mm
Width across flats 1	17 mm

Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10°
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner