



## Double-ended open ring spanner, Width across flats: 24X27mm



### Order data

Order number	619705 24X27
GTIN	4045197673428
Item class	62A

### Description

#### Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

#### Standard:

**DIN 3118 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Width across flats 1	24 mm
maximum ring height $h_{2\max}$	17 mm
maximum ring $\varnothing D_2 \max$	46.4 mm
Spanner length L	258 mm
maximum ring $\varnothing D_1 \max$	42.4 mm
Width across flats 2	27 mm
maximum ring height $h_{1\max}$	16 mm
Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10 degrees

Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner