



Lace-up boot, anthracite STAVANGER Bau GORE II, S3 XB, EU shoe size: 36



Order data

| | |
|--------------|---------------|
| Order number | 092782 36 |
| GTIN | 4044348488003 |
| Item class | 09C |

Description

Version:

STAVANGER Bau GORE II lace-up boots with GORE-TEX® membrane for a breathable but still waterproof upper material made of supple waterproof leather. Good resistance to acids and alkalis. High level of cutting resistance and mechanical strength. Wide tread. Extremely anti-slip, even on smooth, wet and oily floors. With **SECURA VARIO® heel shock absorption** and heat-resistance up to approx. 220°C.

- **Closed tongue.**
- **Perbunan Alpine sole, anthracite.**
- **Reinforced toe protection.**
- **Lace hooks.**
- **Elevated shank.**
- **Padded edges.**
- **Real leather insole.**
- **ERGO-COOL® comfort mid-sole inlay.**

Standard:

EN ISO 20345:2011 S3 SRC CI HRO

Note:

Stock goods in EU shoe sizes 39 – 46, can be ordered in EU shoe sizes 36 – 51.

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):
Over 200 °C

Cold insulation: down to -20°C

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

| | |
|--|--|
| Puncture resistance | Steel |
| Material of protective toe-cap | Steel |
| Standard | Inlay type-tested according to DGUV regulation 191 |
| Behaviour of outer sole in response to contact temperature (melting point of the outer sole) | Over 200 °C |
| EU shoe size | 36 |
| Protection class | S3 |
| Cold insulation | down to -20°C |
| Characteristics | Vario® damping |
| Gender | Gentlemen's |
| Type of product | Safety boots |