

# uvex

## Lace-up boot, black/orange uvex 2, S3, EU shoe size: 35



### Order data

Order number	092136 35
GTIN	4031101609669
Item class	04V

### Description

#### Version:

Lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Distance Mesh lining material.**
- **100 % metal-free uvex xenova® toecap.**
- **Two-layer PU sole with TPU inserts with the best damping characteristics.**
- **PU overcap to protect the upper material, for significantly longer working life.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety shoes of hydrophobic, fully grained smooth leather. With non-metallic penetration-resistant insert.

#### Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Composite

Puncture resistance: Textile

Standard: Inlay type-tested according to DGUV regulation 191

### Technical description

Protection class	S3
EU shoe size	35
Standard	Inlay type-tested according to DGUV regulation 191
Puncture resistance	Textile
Material of protective toe-cap	Composite
Series	uvex 2
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots