



## Shoe, black/silver Black Eagle Safety 41.1 Low ESD, S1P, EU shoe size: 37



### Order data

Order number	092284 37
GTIN	4044465250569
Item class	04Y

### Description

#### Version:

Airy and modern safety shoe for indoors and outdoors. Water repellent.

- **Breathable upper made of microfibre/textile.**
- **Abrasion-resistant and breathable inner lining.**
- **Practical quick release for fast, easy and safe on and off.**
- **Special (washable) insoles for sweat absorption.**
- **Non-slip sole made of rubber.**
- **Heel damping made of PU foam.**
- **ESD security.**

#### Standard:

EN ISO 20345:2011 S1P HRO HI CI WR WRU SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

#### Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 35 – 51.

electrostatic characteristic: EGB/ESD

Protection class: S1P

Material of protective toe-cap: Composite

Puncture resistance: Textile

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200 °C

Standard: Inlay type-tested according to DGUV regulation 191

## Technical description

EU shoe size	37
Standard	Inlay type-tested according to DGUV regulation 191
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Material of protective toe-cap	Composite
Protection class	S1P
Puncture resistance	Textile
Series	Black Eagle Safety
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes