



## Tubular socket wrench, angled, Width across flats: 27 mm



### Order data

Order number	621340 27
GTIN	4045197528261
Item class	62C

### Description

#### Version:

Drop-forged for the most arduous duties with especially close-tolerance jaw widths. Special hollow form, even for nuts on long projecting threads. Same jaw width at each end; on sizes 6 and 7 these are both single hexagon, from size 8 single hexagon at the long leg and bi-hexagon on the short leg. Angled at approx. 90 - 95°.

#### Material:

Chrome vanadium steel, chrome-plated.

Socket length L<sub>1</sub>: 280 mm

Socket length L<sub>2</sub>: 58 mm

Bore Ø F: 22 mm

### Technical description

Socket length L <sub>1</sub>	280 mm
Drive profile long side	Hexagon socket
Bore Ø F	22 mm
Drive profile short side	Bi-hex socket
Width across flats	27 mm
Socket length L <sub>2</sub>	58 mm
Drive profile	Bi-hex socket
Drive profile	Hexagon socket
Angle	90 - 95 degrees

Manufacturing process	forged
Material	Chrome vanadium steel
Surface	chrome-plated
both sides have the same width across flats	yes
Type of product	Socket spanner