

**Cup grinding wheel ceramic D×W×H (mm), 100×50×20, Type: EK80****Order data**

Order number	597025 EK80
GTIN	9003175682652
Item class	53Y

Description**Version:**

Tapered-cup grinding wheel with: **White electro-bonded Aluminium Oxide. Specification: SD83AII7PVK3F steel, universal.**

Advantage:

With all-round synthetic resin impregnation for increased edge stability. **With all-round synthetic resin impregnation** for increased edge stability.

Application:

For sharpening of drills, milling cutters, etc. Wet cutting with emulsion or cutting oil recommended.

Technical description

Grit	80
Grinding medium code	A
Grinding media	White electro-bonded Aluminium Oxide
Specification	SD83AII7PVK3F steel, universal

Grinding process	Tool grinding
Shape	6
Disc Ø D	100 mm
Disc thickness T	50 mm
Product name attribute	100×50×20
Bore Ø H	20 mm
Wall thickness W	10 mm
Floor thickness E	10 mm
Type of product	Tapered cup grinding wheel