



## Shoe, black/green POTENCY ESD, S1P, EU shoe size: 43



### Order data

Order number	092370 43
GTIN	8023796410121
Item class	09M

### Description

#### Version:

POTENCY safety shoes in a modern design.

- **Upper material of breathable fabric/leather combination.**
- **Inner liner 100% polyester, breathable, anti-bacterial, abrasion-resistant.**
- **Perforated and anatomically-compatible shock-absorbent insole of PU.**
- **Outer sole: PU/TPU.**
- **BOA® lacing system.**
- **ESD security.**

#### Standard:

EN ISO 20345:2011 S1P SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

#### Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 36 – 47.

electrostatic characteristic: EGB/ESD

Protection class: S1P

Material of protective toe-cap: Aluminium

Puncture resistance: Textile

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Drejelukning

### Technical description

Puncture resistance	Textile
Standard	Inlay type-tested according to DGUV regulation 191
Material of protective toe-cap	Aluminium
Protection class	S1P
EU shoe size	43
Characteristics	Drejelukning
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes