



Shoe, black/green POTENCY ESD, S1P, EU shoe size: 40



Order data

Order number	092370 40
GTIN	8023796410091
Item class	09M

Description

Version:

POTENCY safety shoes in a modern design.

- **Upper material of breathable fabric/leather combination.**
- **Inner liner 100% polyester, breathable, anti-bacterial, abrasion-resistant.**
- **Perforated and anatomically-compatible shock-absorbent insole of PU.**
- **Outer sole: PU/TPU.**
- **BOA® lacing system.**
- **ESD security.**

Standard:

EN ISO 20345:2011 S1P SRC

Inlay provision design type tested to DGUV regulations 191.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 36 – 47.

Technical description

EU shoe size	40
Protection class	S1P
Material of protective toe-cap	Aluminium
Puncture resistance	Textile

Standard	Inlay type-tested according to DGUV regulation 191
Series	POTENCY
Characteristics	Drejelukning
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes