



Sliding head, 1 inch without handle



Order data

Order number	648200
GTIN	4018754013494
Item class	63A

Description

Version:

Drive sockets to DIN 3120-D 25 with hole.
Sliding head can be moved for the most suitable leverage.

Standard:

DIN 3122-A 25

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Suitable for:

Manual use.

Technical description

Square drive	1 in
overall length	80 mm
Surface	chrome-plated
Type of product	Sliding head

