



Tubular socket wrench, angled, Width across flats: 29 mm



Order data

Order number	621340 29
GTIN	4045197528285
Item class	62C

Description

Version:

Drop-forged for the most arduous duties with especially close-tolerance jaw widths. Special hollow form, even for nuts on long projecting threads. Same jaw width at each end; on sizes 6 and 7 these are both single hexagon, from size 8 single hexagon at the long leg and bi-hexagon on the short leg. Angled at approx. 90 - 95°.

Material:

Chrome vanadium steel, chrome-plated.

Socket length L₁: 300 mm

Socket length L₂: 62 mm

Bore Ø F: 22 mm

Technical description

Bore Ø F	22 mm
Socket length L ₁	300 mm
Width across flats	29 mm
Socket length L ₂	62 mm
Drive profile short side	Bi-hex socket
Drive profile long side	Hexagon socket
Drive profile	Bi-hex socket
Drive profile	Hexagon socket
Angle	90 - 95 degrees

Manufacturing process	forged
Material	Chrome vanadium steel
Surface	chrome-plated
both sides have the same width across flats	yes
Type of product	Socket spanner