



Shoe, black/orange CREGAN, S3S CI FO SR, EU shoe size: 40



Order data

Order number	092378 40
GTIN	8023796648326
Item class	09M

Description

Version:

CREGAN safety shoes.

- **Upper material of water-repellent leather.**
- **Inner lining 100% polyester, breathable, anti-bacterial, abrasion-resistant.**
- **Perforated and anatomically-compatible shock-absorbent insole, made of PU.**
- **Outer sole: PU/TPU.**
- **Overcap of TPU.**

Standard:

EN ISO 20345:2022 S3S CI FO SR

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 36 – 48.

Technical description

Material of protective toe-cap	Aluminium
Protection class	S3S
Puncture resistance	Textile
EU shoe size	40

Standard	Inlay type-tested according to DGUV regulation 191
Characteristics	resistant to fuel
Gender	Gentlemen's
Type of product	Safety shoes