



Tubular socket wrench, angled, Width across flats: 30 mm



Order data

Order number	621340 30
GTIN	4045197528292
Item class	62C

Description

Version:

Drop-forged for the most arduous duties with especially close-tolerance jaw widths. Special hollow form, even for nuts on long projecting threads. Same jaw width at each end; on sizes 6 and 7 these are both single hexagon, from size 8 single hexagon at the long leg and bi-hexagon on the short leg. Angled at approx. 90 - 95°.

Material:

Chrome vanadium steel, chrome-plated.

Socket length L₁: 310 mm

Socket length L₂: 64 mm

Bore Ø F: 24 mm

Technical description

Socket length L ₁	310 mm
Drive profile long side	Hexagon socket
Width across flats	30 mm
Drive profile short side	Bi-hex socket
Socket length L ₂	64 mm
Bore Ø F	24 mm
Drive profile	Bi-hex socket
Drive profile	Hexagon socket
Angle	90 - 95 degrees

Manufacturing process	forged
Material	Chrome vanadium steel
Surface	chrome-plated
both sides have the same width across flats	yes
Type of product	Socket spanner