

**Diamond dished grinding wheel D×T×H (mm), 100×25×20, Type: D126****Order data**

|              |               |
|--------------|---------------|
| Order number | 597710 D126   |
| GTIN         | 9003178154200 |
| Item class   | 53Y           |

**Description****Version:**

**Cup grinding wheels and dished grinding wheels with diamond abrasive coating.**

General-purpose grit for medium to fine surface quality and very good metal removal rates.

**Specification: D126C75B DIAGO W-Carbide.**

**Application:**

**For general use on all common tool grinding machines.** For grinding **carbide tools and short chipping non-ferrous materials**. Very well suited to dry grinding, but can also be used for wet grinding.

**Technical description**

|                      |                          |
|----------------------|--------------------------|
| Grit                 | D126                     |
| Specification        | D126C75B DIAGO W-Carbide |
| Grinding medium code | D                        |
| Grinding process     | Tool grinding            |
| Grinding media       | Diamond                  |

|                                   |             |
|-----------------------------------|-------------|
| Shape                             | 12A2D       |
| Disc Ø D                          | 100 mm      |
| Disc thickness T                  | 25 mm       |
| Product name attribute            | 100×25×20   |
| Bore Ø H                          | 20 mm       |
| Abrasive coating width W end face | 12 mm       |
| Abrasive coating height X         | 3 mm        |
| Type of product                   | Sanding pad |

## User data

|              | Suitability                               | V <sub>c</sub> | ISO code |
|--------------|---|----------------|----------|
| Carbide (HM) | suitable                                  |                |          |
| Plastic, GRP | suitable only under restricted conditions |                |          |
| wet maximum  | suitable only under restricted conditions |                |          |
| dry          | suitable                                  |                |          |