

**C-hook (pin) spanner with square pin, for external nut Ø: 110/115mm****Order data**

| | |
|--------------|----------------|
| Order number | 628400 110/115 |
| GTIN | 4020772054700 |
| Item class | 63Q |

Description**Version:**

Special steel, drive head ground, hardened and burnished.
Hook spanner with square pin to DIN 1810 A.

Application:

For slotted nuts to DIN 1804 and roller bearing slotted nuts to DIN 981.

Note:

Sizes 135/145; 260/270 thickness is different to DIN.

Technical description

| | |
|----------------------------|-----------------------|
| overall length | 335 mm |
| for external nut Ø | 110 - 115 mm |
| Type | 1810A |
| Manufacturer's designation | DIN 1810A |
| Type of product | C-hook (pin) spanners |