

**C-hook (pin) spanner with pin, for external nut Ø: 40/42mm****Order data**

Order number	628500 40/42
GTIN	4020772054939
Item class	63Q

**Description****Version:**

Special steel, drive head ground, hardened and burnished.  
Hook spanner with round pin to DIN 1810 B.

**Application:**

For DIN 1816 capstan nuts.

**Technical description**

overall length	170 mm
for external nut Ø	40 - 42 mm
Pin Ø	4 mm
Type	1810A
Manufacturer's designation	DIN 1810B
Type of product	C-hook (pin) spanners