



## Adjustable C-hook (pin) spanner with square pin, for external nut Ø: 20-35mm



### Order data

Order number	628000 20-35
GTIN	4020772051730
Item class	63Q

### Description

**Version:**

Adjustable C-hook spanner with square pin.  
Special steel, drive head ground, hardened and nickel-plated.

**Application:**

For slotted nuts to DIN 1804 and roller bearing slotted nuts to DIN 981.

### Technical description

overall length	165 mm
for external nut Ø	20 - 35 mm
Type	775D
Manufacturer's designation	775D
Type of product	C-hook (pin) spanners