



## Hardness comparison plate HV 10, Hardness value approx.: 780



### Order data

Order number	495164 780
GTIN	2050001958181
Item class	49L

### Description

#### Version:

High-quality hardness comparison plates of optimised and homogeneous steel for periodic calibration of hardness testers.

#### Advantage:

Colour-coded and symbolic organiser system on all packaging.

#### Supplied with:

Every hardness comparison plate is supplied with a **DAkkS calibration certificate**.

#### Note:

**Calibrations for other processes, hardness comparison plates in other sizes and with pitch lines available on request. Quick availability ex-stock from the manufacturer.**

### Technical description

Hardness value approx.	780
Height	10 mm
Test procedure	HV 10
Ø	65 mm

Test certificate	Manufacturer's test certificate
incl. DAkkS calibration certificate	yes
Packaging	sturdy box
Type of product	Hardness block