




## Hardness comparison plate HV 20, Hardness value approx.: 780



### Order data

Order number	495166 780
GTIN	2050001958259
Item class	49L

### Description

#### Version:

High-quality hardness comparison plates of optimised and homogeneous steel for periodic calibration of hardness testers.

#### Advantage:

Colour-coded and symbolic organiser system on all packaging.

#### Supplied with:

Every hardness comparison plate is supplied with a **DAkkS calibration certificate**.

#### Note:

**Calibrations for other processes, hardness comparison plates in other sizes and with pitch lines available on request. Quick availability ex-stock from the manufacturer.**

### Technical description

Height	10 mm
Test procedure	HV 20
Ø	65 mm
Hardness value approx.	780
Test certificate	Manufacturer's test certificate
incl. DAkkS calibration certificate	yes
Packaging	sturdy box

Type of product

Hardness block