




Hardness comparison plate HV 20, Hardness value approx.: 200



Order data

Order number	495166 200
GTIN	2050001958198
Item class	49L

Description

Version:

High-quality hardness comparison plates of optimised and homogeneous steel for periodic calibration of hardness testers.

Advantage:

Colour-coded and symbolic organiser system on all packaging.

Supplied with:

Every hardness comparison plate is supplied with a **DAkkS calibration certificate**.

Note:

Calibrations for other processes, hardness comparison plates in other sizes and with pitch lines available on request. Quick availability ex-stock from the manufacturer.

Technical description

Height	10 mm
Hardness value approx.	200
Ø	65 mm
Test procedure	HV 20
Test certificate	Manufacturer's test certificate
incl. DAkkS calibration certificate	yes
Packaging	sturdy box

Type of product

Hardness block