

**C-hook (pin) spanner with square pin, for external nut Ø: 52/55mm****Order data**

Order number	628400 52/55
GTIN	4020772054656
Item class	63Q

**Description****Version:**

Special steel, drive head ground, hardened and burnished.  
Hook spanner with square pin to DIN 1810 A.

**Application:**

For slotted nuts to DIN 1804 and roller bearing slotted nuts to DIN 981.

**Note:**

Sizes 135/145; 260/270 thickness is different to DIN.

**Technical description**

overall length	206 mm
for external nut Ø	52 - 55 mm
Type	1810A
Manufacturer's designation	DIN 1810A
Type of product	C-hook (pin) spanners