



Adjustable C-hook (pin) spanner with square pin, for external nut \varnothing : 35-60 mm



Order data

| | |
|--------------|---------------|
| Order number | 628000 35-60 |
| GTIN | 4020772051747 |
| Item class | 63Q |

Description

Version:

Adjustable C-hook spanner with square pin.
Special steel, drive head ground, hardened and nickel-plated.

Application:

For slotted nuts to DIN 1804 and roller bearing nuts to DIN 981.
for external nut \varnothing : 35 - 60 mm
overall length: 210 mm

Technical description

| | |
|--------------------------------|-----------------------|
| for external nut \varnothing | 35 - 60 mm |
| overall length | 210 mm |
| Type | 775D |
| Manufacturer's designation | 775D |
| Type of product | C-hook (pin) spanners |