

**Adjustable C-hook (pin) spanner with pin, largest \varnothing / pin \varnothing : 155/8mm****Order data**

Order number	628100 155/8
GTIN	4020772053192
Item class	63Q

Description**Version:**

Adjustable C-hook pin spanner.
Special steel, drive head ground, hardened and burnished.

Application:

For capstan nuts to DIN 1816.

Technical description

largest \varnothing	155 mm
for external nut \varnothing	95 - 155 mm
Pin \varnothing	8 mm
overall length	335 mm
Type	775D
Manufacturer's designation	776C
Type of product	C-hook (pin) spanners