

**C-hook (pin) spanner with square pin, for external nut Ø: 58/62mm****Order data**

Order number	628400 58/62
GTIN	4020772054663
Item class	63Q

Description**Version:**

Special steel, drive head ground, hardened and burnished.
Hook spanner with square pin to DIN 1810 A.

Application:

For slotted nuts to DIN 1804 and roller bearing slotted nuts to DIN 981.

Note:

Sizes 135/145; 260/270 thickness is different to DIN.

Technical description

for external nut Ø	58 - 62 mm
overall length	240 mm
Type	1810A
Manufacturer's designation	DIN 1810A
Type of product	C-hook (pin) spanners