

**Adjustable C-hook (pin) spanner with pin, largest  $\varnothing$  / pin  $\varnothing$ : 230/10mm****Order data**

Order number	628100 230/10
GTIN	4020772053109
Item class	63Q

**Description****Version:**

Adjustable C-hook pin spanner.  
Special steel, drive head ground, hardened and burnished.

**Application:**

For capstan nuts to DIN 1816.

**Technical description**

for external nut $\varnothing$	165 - 230 mm
overall length	460 mm
largest $\varnothing$	230 mm
Pin $\varnothing$	10 mm
Type	775D
Manufacturer's designation	776C
Type of product	C-hook (pin) spanners