



Adjustable C-hook (pin) spanner with square pin, for external nut \varnothing : 155-230mm



Order data

Order number	628000 155-230
GTIN	4020772051778
Item class	63Q

Description

Version:

Adjustable C-hook spanner with square pin.
Special steel, drive head ground, hardened and nickel-plated.

Application:

For slotted nuts to DIN 1804 and roller bearing slotted nuts to DIN 981.

Technical description

overall length	460 mm
for external nut \varnothing	155 - 230 mm
Type	775D
Manufacturer's designation	775D
Type of product	C-hook (pin) spanners