



Flexible head wrench, Width across flats: 10X11 mm



Order data

Order number	621400 10X11
GTIN	4018754025664
Item class	63A

Description

Version:

Drop-forged; precisely toleranced jaw widths; bi-hexagon. An integral compression spring keeps the heads in the respective position.

Strong double T-profile shank; with thin-walled, deep AS-Drive profile socket heads. Swivel heads (movement up to 220°).

Material:

Chrome alloy steel, chrome-plated, smoothed finish (no sharp edges).

Technical description

Head Ø D ₁	14.7 mm
Head Ø D ₂	15.9 mm
Spanner length L	202 mm
Width across flats 2	11 mm
Width across flats 1	10 mm
Drive profile	Bi-hex socket
Type of product	Socket spanner