

## “Go” / “No Go” plug gauge with numerical tolerance with wear allowance, Type: H



### Order data

Order number	484026 H
GTIN	2050001952523
Item class	48B

### Description

#### IMPORTANT: item is configurable

Tolerance zone: A; B; C; CD; D; E; EF; F; FG; G; H; J; JS; K; M; N; P; R; S; T; U; V; X; Y; Z; ZA; ZB; ZC

Quality: 10; 11; 12; 13; 6; 7; 8; 9

Nominal size: 40.001 - 50 mm, Intervall: 0,001

#### Version:

Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped. The “Go” ends of these working gauges have a wear allowance to DIN 7164.

“Go” / “No Go” plug gauge with numerical tolerance, e.g. 484026 **28 + 0.01 / - 0.02**.

#### Standard:

Toleranz und Abmaße nach **DIN 1938-1, DIN 2245-1 und DIN 7164**.

#### Note:

- **Please state the exact nominal  $\varnothing$  with tolerance band (A-ZC) and quality (6-13) or numeric tolerance ( $\pm$ ).**
- **Intermediate size plug gauges are just double-ended plug gauges in fractional sizes!**
- **For whole number (even)  $\varnothing$  with ISO fits see No. 484000; 484020; 484040 or on request.**
- **For acceptance gauges (without wear allowance) see No. 484027; 484028.**

Calibration: L6

Nominal size: 40.001 - 50 mm

### Technical description

Tolerance zone	A
Tolerance zone	G
Tolerance zone	H

Tolerance zone	J
Tolerance zone	K
Tolerance zone	M
Tolerance zone	N
Tolerance zone	P
Tolerance zone	R
Tolerance zone	S
Tolerance zone	B
Tolerance zone	T
Tolerance zone	U
Tolerance zone	V
Tolerance zone	X
Tolerance zone	Y
Tolerance zone	Z
Tolerance zone	ZA
Tolerance zone	C
Tolerance zone	D
Tolerance zone	E
Tolerance zone	F
Tolerance zone	JS
Tolerance zone	CD
Tolerance zone	EF
Tolerance zone	FG
Tolerance zone	ZB
Tolerance zone	ZC
Tolerance value	-1.95 - 3.9
Standard	DIN 7164
Standard	DIN 2245-1
Standard	DIN EN ISO 1938-1

Quality	11
Quality	10
Quality	12
Quality	13
Quality	9
Quality	7
Quality	6
Quality	8
Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Nominal size	40.001 - 50 mm
Calibration	L6
Type of product	Pug Gauge

## Services

Labelling laser-etched Type	018940
DAkkS calibration "Go" / "No Go" plug gauge maximum $\varnothing$ 60 mm	019620 60
Calibration "Go" / "No Go" plug gauge maximum $\varnothing$ 60 mm	018400 60
Calibration "Go" / "No Go" plug gauge maximum $\varnothing$ 60 mm	028300 60
DAkkS calibration "Go" / "No Go" plug gauge maximum $\varnothing$ 60 mm	028340 60