

“Go” / “No Go” plug gauge with numerical tolerance with wear allowance, Type: I



Order data

Order number	484026 I
GTIN	2050001952530
Item class	48B

Description

IMPORTANT: item is configurable

Tolerance zone: A; B; C; CD; D; E; EF; F; FG; G; H; J; JS; K; M; N; P; R; S; T; U; V; X; Y; Z; ZA; ZB; ZC

Quality: 10; 11; 12; 13; 6; 7; 8; 9

Nominal size: 50.001 - 60 mm, Intervall: 0,001

Version:

Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped.

The “Go” ends of these working gauges have a wear allowance to DIN 7164.

“Go” / “No Go” plug gauge with numerical tolerance, e.g. 484026 **28 + 0.01 / - 0.02**.

Standard:

Toleranz und Abmaße nach **DIN 1938-1, DIN 2245-1 und DIN 7164**.

Note:

- **Please state the exact nominal \varnothing with tolerance band (A-ZC) and quality (6-13) or numeric tolerance (\pm).**
- **Intermediate size plug gauges are just double-ended plug gauges in fractional sizes!**
- **For whole number (even) \varnothing with ISO fits see No. 484000; 484020; 484040 or on request.**
- **For acceptance gauges (without wear allowance) see No. 484027; 484028.**

Calibration: L6

Nominal size: 50.001 - 60 mm

Technical description

Tolerance zone	A
Tolerance zone	G
Tolerance zone	H

Tolerance zone	J
Tolerance zone	K
Tolerance zone	M
Tolerance zone	N
Tolerance zone	P
Tolerance zone	R
Tolerance zone	S
Tolerance zone	B
Tolerance zone	T
Tolerance zone	U
Tolerance zone	V
Tolerance zone	X
Tolerance zone	Y
Tolerance zone	Z
Tolerance zone	ZA
Tolerance zone	C
Tolerance zone	D
Tolerance zone	E
Tolerance zone	F
Tolerance zone	JS
Tolerance zone	CD
Tolerance zone	EF
Tolerance zone	FG
Tolerance zone	ZC
Tolerance zone	ZB
Tolerance value	-2.3 - 4.6
Standard	DIN 7164
Standard	DIN 2245-1
Standard	DIN EN ISO 1938-1

Quality	11
Quality	8
Quality	12
Quality	7
Quality	6
Quality	10
Quality	9
Quality	13
Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Nominal size	50.001 - 60 mm
Calibration	L6
Type of product	Pug Gauge

Services

Labelling laser-etched Type	018940
Calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	018400 60
DAkkS calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	019620 60
Calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	028300 60
DAkkS calibration "Go" / "No Go" plug gauge maximum Ø 60 mm	028340 60