

Groove width gauge with numerical tolerance, Type: A



Order data

| | |
|--------------|---------------|
| Order number | 484408 A |
| GTIN | 2050001956576 |
| Item class | 48B |

Description

IMPORTANT: item is configurable

Nominal size: 3.001 - 5.999 mm

Tolerance zone: A; B; C; CD; D; E; EF; F; FG; G; H; J; JS; K; M; N; P; R; S; T; U; V; X; Z; ZA; ZB; ZC; ZC

Quality: 10; 11; 12; 13; 7; 8; 9

Version:

For intermediate sizes or numerical tolerances.

Groove width gauges with "Go" and "No Go" end. "Go" end with **wear allowance** to DIN 7164.

Gauge body of hardened steel.

Application:

For checking flat fits, e. g. grooves.

Standard:

Toleranzen und Abmaße nach **DIN 1938-1, DIN 2245-1 und DIN 7163.**

Note:

Example: 15.8 m6 or 41.04 + 0.01 / - 0.02.

Calibration: L6

Nominal size: 3.001 - 5.999 mm

Technical description

| | |
|----------------|------------------|
| Nominal size | 3.001 - 5.999 mm |
| Tolerance zone | A |
| Tolerance zone | B |
| Tolerance zone | C |

| | |
|----------------|----|
| Tolerance zone | CD |
| Tolerance zone | D |
| Tolerance zone | E |
| Tolerance zone | EF |
| Tolerance zone | F |
| Tolerance zone | FG |
| Tolerance zone | G |
| Tolerance zone | H |
| Tolerance zone | J |
| Tolerance zone | JS |
| Tolerance zone | M |
| Tolerance zone | K |
| Tolerance zone | N |
| Tolerance zone | P |
| Tolerance zone | S |
| Tolerance zone | R |
| Tolerance zone | T |
| Tolerance zone | U |
| Tolerance zone | X |
| Tolerance zone | V |
| Tolerance zone | ZC |
| Tolerance zone | Z |
| Tolerance zone | ZA |
| Tolerance zone | ZC |
| Tolerance zone | ZB |
| Quality | 7 |
| Quality | 8 |
| Quality | 9 |
| Quality | 10 |

| | |
|----------------|----|
| Quality | 11 |
| Quality | 12 |
| Quality | 13 |
| Tolerance zone | A |
| Tolerance zone | G |
| Tolerance zone | H |
| Tolerance zone | J |
| Tolerance zone | K |
| Tolerance zone | M |
| Tolerance zone | N |
| Tolerance zone | P |
| Tolerance zone | R |
| Tolerance zone | S |
| Tolerance zone | B |
| Tolerance zone | T |
| Tolerance zone | U |
| Tolerance zone | V |
| Tolerance zone | X |
| Tolerance zone | Y |
| Tolerance zone | Z |
| Tolerance zone | A |
| Tolerance zone | ZB |
| Tolerance zone | ZC |
| Tolerance zone | C |
| Tolerance zone | D |
| Tolerance zone | E |
| Tolerance zone | F |
| Tolerance zone | CD |
| Tolerance zone | EF |

| | |
|-----------------|------------------|
| Tolerance zone | FG |
| Tolerance zone | JS |
| Calibration | L6 |
| Type of product | Shaft slot gauge |

Services

| | |
|---|-----------|
| Calibration "Go" / "No Go" plug gauge maximum \varnothing 20 mm | 018400 20 |
| DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm | 019620 60 |
| Labelling laser-etched Type | 018940 |
| DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm | 028340 60 |
| Calibration "Go" / "No Go" plug gauge maximum \varnothing 20 mm | 028300 20 |