

**Carbide-tipped multi-purpose drill set, Drill Ø: 4-10mm****Order data**

| | |
|--------------|---------------|
| Order number | 787050 4-10 |
| GTIN | 9002741011346 |
| Item class | 76G |

Description**Version:**

The carbide insert is diamond ground all round, giving **extra-sharp, super-hard cutting edges**. Patented 4-step profile for quick removal of chips and swarf.

Application:

Precise **drilling** in tiles, masonry and concrete, metal, wood, and plastics.

Content:

1 each drill: Size (Ø) 4; 5; 6; 8; 10 mm

Note:

Caution - only for rotary use (without hammer action!)

Technical description

| | |
|---------------------------|-----------|
| Number of drills | 5 |
| Drill Ø | 4 - 10 mm |
| Number of cutting edges Z | 2 |
| Tool material | Carbide |

| | |
|----------------------------------|-------------------------|
| Use with impact / without impact | not for impact drilling |
| Shank | Plain shank |
| Type of product | Multi-purpose drill |

Accessories

| | |
|--|-----------|
| Carbide-tipped multi-purpose drill Drill Ø 10 mm | 787040 10 |
| Carbide-tipped multi-purpose drill Drill Ø 5 mm | 787040 5 |
| Carbide-tipped multi-purpose drill Drill Ø 6 mm | 787040 6 |
| Carbide-tipped multi-purpose drill Drill Ø 4 mm | 787040 4 |
| Carbide-tipped multi-purpose drill Drill Ø 8 mm | 787040 8 |