




Carbide-tipped multi-purpose drill set long, Drill Ø: 6-12mm



Order data

Order number	787055 6-12
GTIN	9002741072880
Item class	76G

Description

Version:

The carbide insert is diamond ground all round, giving **extra-sharp, super-hard cutting edges**. Patented 4-step profile for quick removal of chips and swarf. Overall length 400 mm, flute length 300 mm.

Application:

Precise **drilling** in tiles, masonry and concrete, metal, wood, and plastics.

Content:

1 each drill: Size (Ø) 6; 8; 10; 12 mm

Note:

Caution - only for rotary use (without hammer action!)

Technical description

Number of drills	4
Drill Ø	6 - 12 mm
Number of cutting edges Z	2
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Shank	Plain shank
Type of product	Multi-purpose drill

Accessories

Carbide-tipped multi-purpose drilllong Drill Ø 8 mm	787045 8
Carbide-tipped multi-purpose drilllong Drill Ø 10 mm	787045 10
Carbide-tipped multi-purpose drilllong Drill Ø 12 mm	787045 12
Carbide-tipped multi-purpose drilllong Drill Ø 6 mm	787045 6