



Carbide-tipped multi-purpose drill set, Number of drills: 7



Order data

Order number	787010 7
GTIN	4002395369942
Item class	76G

Description

Version:

Carbide tip **with ground point and multi-purpose cutter angle**. The centrally ground chisel **edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

Application:

For drilling various materials, also in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

Content:

Drill No. 787000: 1 pc. each
size (Ø) 3; 4; 5; 6; 6; 8; 10

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Shank: Plain shank

Technical description

Drill Ø	3 - 10 mm
---------	-----------

Number of drills	7
Number of cutting edges Z	2
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Shank	Plain shank
Type of product	Multi-purpose drill

Accessories

Carbide-tipped multi-purpose drill Drill Ø 4 mm	787000 4
Carbide-tipped multi-purpose drill Drill Ø 8 mm	787000 8
Carbide-tipped multi-purpose drill Drill Ø 3 mm	787000 3
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787000 6
Carbide-tipped multi-purpose drill Drill Ø 10 mm	787000 10
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787000 5