



Fine stoneware drill /tiles drill, Drill Ø: 6mm



Order data

Order number	787035 6
GTIN	9002741151356
Item class	76G

Description

Version:

2 pieces. A drill with a **diamond-ground carbide tip** with a patented centring tip for highly accurate start positioning and exact holes without break-outs. With 10 mm shank. A carbide drill for use in standard drill chucks. With 1/4 inch (E 6.3) hexagon shank.

Application:

For **very hard stoneware tiles** up to Mohs / scratch hardness class 9 and for glass and porcelain.

Note:

Not suitable for hammer drills. Maximum spindle speed 200 rpm. No cooling required.

Technical description

Use with impact / without impact	not for impact drilling
Number of drills	2
Drill Ø	6 mm
overall length	115 mm
Shank	Plain shank

maximum speed	200 min ⁻¹
Tool material	Carbide
Shank Ø	10
Bit hexagon shank	E 6,3
Type of product	Masonry drill