



Carbide masonry drill, Drill Ø: 9 mm



Order data

Order number	786000 9
GTIN	4002395332137
Item class	76G

Description

Version:

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

Hammer and rotary bits with strong carbide cutter tip.

Application:

Primarily for **drilling fastening holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic. Also suitable for drilling hardened steel due to corrected cutting edge.

Shank: Plain shank

Flute length: 80 mm

overall length: 120 mm

Shank Ø: 9 mm

Technical description

overall length	120 mm
Flute length	80 mm
Drill Ø	9 mm
Number of cutting edges Z	2
Shank Ø	9 mm
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039

Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill