



## Carbide-tipped multi-purpose drill long with SDS-plus shank socket, Drill Ø: 8 mm



### Order data

Order number	787060 8
GTIN	4002395353491
Item class	76G

### Description

#### Version:

Carbide tip **with ground point and multi-purpose cutter angle. The centrally ground chisel edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

#### Application:

For drilling various materials, also in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

#### Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Shank: SDS Plus

Flute length: 150 mm

overall length: 210 mm

### Technical description

Flute length	150 mm
Drill Ø	8 mm
overall length	210 mm
Number of cutting edges Z	2
Tool material	Carbide
Use with impact / without impact	not for impact drilling

Shank	SDS Plus
Type of product	Multi-purpose drill