



## Carbide masonry drill, Drill Ø: 9,5 mm



### Order data

Order number	786000 9,5
GTIN	4002395365777
Item class	76G

### Description

#### Version:

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

#### Application:

Primarily for **drilling fastening holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic. Also suitable for drilling hardened steel due to corrected cutting edge.

Shank: Plain shank

Flute length: 80 mm

overall length: 120 mm

Shank Ø: 9.5 mm

### Technical description

Flute length	80 mm
overall length	120 mm
Drill Ø	9.5 mm
Number of cutting edges Z	2
Shank Ø	9.5 mm
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039

Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill