




High-performance heavy-duty side cutter TwinForce®, polished, with grips, overall length: 180mm



Order data

Order number	723180 180
GTIN	4003773074779
Item class	73F

Description

Version:

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with eccentric double-joint design.

Pliers chemically blacked, head bright polished, handles with multi-component covering.

Advantage:

Superior heavy-duty side cutter requiring 50 % less applied force than conventional heavy-duty side cutters of the same size. Set-back jaws reduce the force required.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	180 mm
Cutting capacity soft wire up to Ø	5.5 mm
Cutting capacity hard wire up to Ø	3.2 mm
Cutting capacity piano wire up to Ø	3 mm
Manufacturer's designation	TwinForce
Standard	DIN ISO 5749
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	Jaws chemically blackened, head bright polished
Heavy-duty diagonal side cutter	yes
with selectable return spring	no
Type of product	Cutting pliers