



Carbide-tipped multi-purpose drill, Drill Ø: 4 mm



Order data

Order number	787000 4
GTIN	4002395378098
Item class	76G

Description

Version:

Carbide tip **with ground point and multi-purpose cutter angle**. The **centrally ground chisel edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

Application:

For drilling various materials, also in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Shank: Plain shank

Flute length: 50 mm

overall length: 85 mm

Technical description

Drill Ø	4 mm
overall length	85 mm
Flute length	50 mm
Number of cutting edges Z	2
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Shank	Plain shank

Type of product

Multi-purpose drill