

**Mechanic's side cutter, chrome-plated, overall length: 125mm****Order data**

Order number	724000 125
GTIN	4003773018506
Item class	73F

Description**Version:**

With slim head and induction hardened cutting edges. Cutter edge hardness approx. 63 HRC.
Flush fitting joint with no play.
Pliers chrome-plated, plastic coated handles.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

Cutting capacity piano wire up to Ø	0.6 mm
Cutting capacity soft wire up to Ø	2.5 mm
Cutting capacity hard wire up to Ø	1 mm
overall length	125 mm
with selectable return spring	no
with return spring	no
Standard	DIN ISO 5749
Handle	plastic coated

Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Cutting pliers