



Spring hose clamp pliers, overall length: 250mm



Order data

Order number	719965 250
GTIN	4003773077329
Item class	73F

Description

Version:

Based on the drop-forged Cobra® water pump pliers with push-button fine step adjustment. With special jaws to hold self-clamping hose clips; **jaws can be turned through 360°**. Pliers chemically blacked.

Advantage:

Improved leverage means less force needs to be applied. Jaw opening up to 80 mm.

Application:

For secure gripping of self-clamping hose clips, standard, low-profile and wire clips together with flat spring clamping rings.

Technical description

Opening width	80 mm
Number of fine adjustment steps	25
overall length	250 mm
with parking brake	no
Jaw capacity	≥ 40 mm
Nominal size	70 mm
max. clamping travel	40 mm
Type of handle	plastic coated
Material	Chrome vanadium electro-steel, forged, oil-hardened

Surface of pliers	chemically greyed
Jaws can be rotated through 360°	yes
Quick adjustment	yes
Type of product	Forceps