



Heavy-duty side cutter, chrome-plated, with grips, overall length: 200mm



Order data

Order number	723100 200
GTIN	4003773035367
Item class	73F

Description

Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage.

Jaws chrome-plated, handles with multi-component covering.

Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Cutting capacity soft wire up to \varnothing : 4.2 mm

Cutting capacity hard wire up to \varnothing : 3 mm

Cutting capacity piano wire up to \varnothing : 2.5 mm

Technical description

Cutting capacity soft wire up to \varnothing	4.2 mm
overall length	200 mm
Cutting capacity hard wire up to \varnothing	3 mm
Cutting capacity piano wire up to \varnothing	2.5 mm
Standard	DIN ISO 5749
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers