

**Heavy-duty side cutter, chrome-plated, with grips, overall length: 200mm****Order data**

| | |
|--------------|---------------|
| Order number | 723100 200 |
| GTIN | 4003773035367 |
| Item class | 73F |

Description**Version:**

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage.

Jaws chrome-plated, handles with multi-component covering.

Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

| | |
|-------------------------------------|---|
| Cutting capacity soft wire up to Ø | 4.2 mm |
| overall length | 200 mm |
| Cutting capacity hard wire up to Ø | 3 mm |
| Cutting capacity piano wire up to Ø | 2.5 mm |
| Standard | DIN ISO 5749 |
| Handle | Multi-component covering |
| Manufacturing process | Cutting edges induction hardened (approx. 64 HRC) |

| | |
|---------------------------------|-------------------------|
| Material | Chromium vanadium steel |
| Surface | chrome-plated |
| Heavy-duty diagonal side cutter | no |
| with selectable return spring | no |
| Type of product | Cutting pliers |