



Carbide-tipped multi-purpose drill, Drill Ø: 6 mm



Order data

Order number	787000 6
GTIN	4002395378135
Item class	76G

Description

Version:

Carbide tip **with ground point and multi-purpose cutter angle**. The centrally ground chisel **edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

Application:

For drilling various materials, also in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Shank: Plain shank

Flute length: 60 mm

overall length: 100 mm

Technical description

overall length	100 mm
Flute length	60 mm
Drill Ø	6 mm
Number of cutting edges Z	2
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Shank	Plain shank

Type of product

Multi-purpose drill