



Heavy-duty side cutter, bright finish, overall length: 180mm



Order data

Order number	723400 180
GTIN	4045197166258
Item class	72B

Description

Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage.

Jaws bright finished, plastic coated handles.

Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	3.8 mm
overall length	180 mm
Cutting capacity hard wire up to Ø	2.7 mm
Cutting capacity piano wire up to Ø	2.2 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)

Material	Chromium vanadium steel
Surface	bright finish
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers