



Bolt cropper with coated grips, overall length: 200mm



Order data

Order number	722010 200
GTIN	4003773067047
Item class	73F

Description

Version:

Induction hardened cutting edges (approx. 64 HRC), extreme leverage so less force needs to be applied.

Pliers chemically blacked, head bright polished, handles with multi-component covering.

Standard:

DIN ISO 5743

Material:

Vanadium electro-steel, forged and multi-stage oil-hardened.

Technical description

overall length	200 mm
Cutting capacity piano wire up to Ø	3 mm
Cutting capacity soft wire up to Ø	1 - 6 mm
Cutting capacity hard wire up to Ø	3.5 mm
Standard	DIN ISO 5743
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chrome vanadium high-performance steel
Surface	chemically blacked

Head	polished
Type of product	Cutting pliers