



## Heavy-duty side cutter, polished, overall length: 140mm



### Order data

Order number	723150 140
GTIN	4003773039747
Item class	73F

### Description

#### Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage.

Jaws chemically blacked, polished head, plastic coated handles.

#### Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

#### Standard:

**DIN ISO 5749**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

### Technical description

Cutting capacity hard wire up to Ø	2 mm
Cutting capacity soft wire up to Ø	3.1 mm
Cutting capacity piano wire up to Ø	1.5 mm
overall length	140 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)

Material	Chromium vanadium steel
Surface	chemically blackened, head bright polished
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers