



## Heavy-duty side cutter, polished, overall length: 160mm



### Order data

Order number	723150 160
GTIN	4003773033141
Item class	73F

### Description

#### Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage. Jaws chemically blacked, polished head, plastic coated handles.

#### Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

#### Standard:

**DIN ISO 5749**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

### Technical description

Cutting capacity hard wire up to Ø	2.5 mm
overall length	160 mm
Cutting capacity soft wire up to Ø	3.4 mm
Cutting capacity piano wire up to Ø	2 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)

Material	Chromium vanadium steel
Surface	chemically blackened, head bright polished
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers